

DairyRO

High Performance Dairy Process Membranes

Hydranautics' 40+ years of reverse osmosis membrane manufacturing experience is incorporated into every DairyRO membrane and element. All Dairy RO elements are automation-rolled for straight and minimally sized glue lines, maximum membrane area, and the strongest possible glue line adhesion.

DairyRO composite polyamide reverse osmosis elements are of the net-wrapped, full-fit design, intended for daily CIP in the dairy environment. All membranes and elements are manufactured using highly controlled, ISO 9001-compliant processes, ensuring the highest quality and most consistent, reliable performance available. Experience a new level of product confidence, cost savings and technology excellence with DairyRO.

Key benefits:

- Hydranautics' ultra-high rejection RO membranes provide maximum protein and lactose rejection
- Elements meet FDA regulation CFR Title 21 and 3A Sanitary Standards for Crossflow Membrane Modules, Number 45-01, Section C.
- USDA Accepted – sizes 3838, 3840, 6338, and 8038
- 100% testing of membrane rolls with 1500 ppm NaCl for flux and rejection
- 100% testing of elements for rejection and flow

Key Features:

- New robot-rolling procedure used in the manufacture of DairyRO elements ensure
 - ✓ Superior glue-line adhesion and strength
 - ✓ Tighter rolling and caging performance
 - ✓ Greater flow rates due to smaller glue lines
 - ✓ More structural reliability

Applications:

- Pre-concentrating milk or whey for reducing product transport costs
- Lactose production
- Sweet/acid whey concentration
- Concentration of UF permeate
- Milk and juice concentrations



Type:

Configuration	Sanitary (Full-Fit) Spiral Wound
Membrane Polymer	Composite Polyamide


Application Data:

Maximum Applied Pressure	800 psig (55.0 bar)
Maximum Chlorine Concentration	< 0.1 PPM
Maximum Operating Temperature	122°F (50°C)
Operating pH Range	2.0 - 11.0
Cleaning pH Range	1.0 – 11.5
Maximum Pressure Drop for a vessel	60 psi (4.1 bar)


Product and Guidelines:

Model	Feed Spacer inches (cm)	Area ft ² (m ²)	Dimensions, inches (cm)			Max. Feed Flow, GPM (m ³ /hr)	Max. Pressure Drop per Element, psi (bar)
			A	B	C		
DairyRO 3838-30	0.030 (0.076)	80 (7.4)	38.00 (96.5)	3.78 (9.6)	0.83 (2.11)	30 (6.9)	15 (1.0)
DairyRO 3838-46	0.046 (0.117)	60 (5.6)	38.00 (96.5)	3.78 (9.6)	0.83 (2.11)	30 (6.9)	15 (1.0)
DairyRO 3838-65	0.065 (0.165)	50 (4.5)	38.00 (96.5)	3.78 (9.6)	0.83 (2.11)	30 (6.9)	15 (1.0)
DairyRO 3840-30	0.030 (0.076)	80 (7.4)	38.75 (98.4)	3.78 (9.6)	0.83 (2.11)	30 (6.9)	15 (1.0)
DairyRO 3840-46	0.046 (0.117)	60 (5.6)	38.75 (98.4)	3.78 (9.6)	0.83 (2.11)	30 (6.9)	15 (1.0)
DairyRO 3840-65	0.065 (0.165)	50 (4.5)	38.75 (98.4)	3.78 (9.6)	0.83 (2.11)	30 (6.9)	15 (1.0)
DairyRO 6338-30	0.030 (0.076)	200 (19)	38.00 (96.5)	6.36 (16.2)	1.138 (2.89)	70(15.8)	15 (1.0)
DairyRO 6338-46	0.046 (0.117)	150 (14)	38.00 (96.5)	6.36 (16.2)	1.138 (2.89)	70(15.8)	15 (1.0)
DairyRO 8038-30	0.030 (0.076)	360 (33)	38.00 (96.5)	7.90 (20.1)	1.125 (2.86)	80 (18.2)	13 (0.9)
DairyRO 8038-46	0.046 (0.117)	280 (26)	38.00 (96.5)	7.90 (20.1)	1.125 (2.86)	80 (18.2)	13 (0.9)
DairyRO 8038-65	0.065 (0.165)	215 (20)	38.00 (96.5)	7.90 (20.1)	1.125 (2.86)	80 (18.2)	13 (0.9)
Hydrapolish 8*	0.030 (0.076)	360 (33)	40.00 (106)	7.90 (20.1)	1.125 (2.86)	80 (18.2)	13 (0.9)

*Hydrapolish 8 provided with one interconnector assembly, two anti-telescoping devices and one brine seal



3838, 3840, 8038 Style



8040 Style with ATDs

Solutions You Need.

Technologies You Trust!

Hydranautics Corporate Office:

401 Jones Road, Oceanside, CA 92058, USA 1-8000-CPA-PURE Phone: 760-901-2500 Fax: 760-901-2578 Email: info@hydranautics.com

Website: www.membranes.com

Americas Hydranautics	Europe/Africa Hydranautics	Middle East Hydranautics	Indian Subcontinent Hydranautics	S.E. Asia/Australia Nitto Denko	Japan Hydranautics- Nitto Denko Corp.
401 Jones Road Oceanside, CA 92058, USA Tel: +760-901- 2500 Tel: 1-800-CPA- PURE Fax: +760-901- 2578	Wilhelmina Singel 116, NL 6221 BL Maastricht, The Netherlands Tel: +31-(0) 43-350 3470 Fax: +31-(0)43-350 3489	DAFZ, Building No.6WA, Office No.828, PO Box 29 38 35, Dubai - UAE Tel: +971 4 2146820/1 Fax: +971 4 2146822	407, Palm Springs Center, Link Road, Malad (West), Mumbai 400 064, India Tel:+91-22- 40030500 Fax: +91-22- 40030496	(Singapore) Pte Ltd 3 Temasek Ave. # 07-01/05 Centennial Towers, Singapore 169074 Tel: +65-6879-3820 Fax: +65-6223-7690	61-7, Azasasadani, Yamadera Kusatsu, Shiga, 525-0042, Japan Tel: +81-77-565-3656 Fax: +81-77-565-3515